

## FM EXPERTPRO 50/ P

Compact FM ExpertPro 50/ P cleaning trolley, suitable for preconditioned cleaning. Securely sealed area for buckets and disposal compartments as well as equipment and cleaning agents.



**Order no.** 1.321-008.0

- Preconditioning with 2 × 12-litre buckets
- Compact version
- 2 × FlexoLink S, 1 × FlexoLink XL

### Technical data

|                            |          |                   |
|----------------------------|----------|-------------------|
| EAN code                   |          | 4054278818511     |
| Programme                  |          | ADVANCED          |
| Colour                     |          | anthracite        |
| Quantity                   | Piece(s) | 1                 |
| Weight without accessories | kg       | 28.2              |
| Package weight             | kg       | 36.5              |
| Dimensions (L × W × H)     | mm       | 1051 × 564 × 1230 |
| Dimensions, packaged       | mm       | 1134 × 584 × 513  |

### Equipment

|                             |   |
|-----------------------------|---|
| Waste disposal              | ■ |
| Enclosed trolley with doors | ■ |

■ Included in the scope of supply.




**FlexoGrip:** ergonomically height-adjustable, relieving shoulders and wrists from strain

Enclosed all around, ideal for cleaning in hygiene-sensitive areas

Brakes on two wheels secure the trolley even on sloping ground

## ACCESSORIES FOR FM EXPERTPRO 50/ P

### 1.321-008.0



|                                     |    | Order no.   | Description  |   |
|-------------------------------------|----|-------------|--|---|
| TROLLEYS & BUCKET SYSTEMS           |    |             |  |   |
| Disposal                            |    |             |  |   |
| Disposal unit, large 2 × 70 L       | 1  | 2.855-268.0 | The disposal module provides space for two 70-l bin liners, is quick and easy to attach, ensuring optimum hygienic waste management.   | ■ |
| Bin liner holder without handle     | 2  | 2.855-225.0 | The bin liner holder without a handle forms a practical disposal module on the outside of the cleaning trolley.                        | □ |
| Foot pedal for Expert and ExpertPro | 3  | 2.855-242.0 | A practical foot pedal allows the lid to be opened ergonomically and effortlessly.   | □ |
| Disposal unit, large, 2 × 120 L     | 4  | 2.855-267.0 | The disposal module offers space for two 120-l bin liners, is quick and easy to attach for optimum hygienic waste management.          | □ |
| Disposal unit, large 3 × 70 L       | 5  | 2.855-269.0 | The disposal module provides space for three 70-l bin liners, is quick and easy to attach, ensuring optimum hygienic waste management. | □ |
| Disposal unit, small 2 × 70 L       | 6  | 2.855-280.0 | The disposal module has space for two 70-l bin liners and is ideal for practical use in the corresponding bin liner holder.            | □ |
| Rubbish bag with zip, red, 120 l    | 7  | 6.999-160.0 | Plastic rubbish bag. Can be used for Clean Liner Classic Trolleys.   | □ |
| Rubbish bag with zip, blue, 120 l   | 8  | 6.999-161.0 |  | □ |
| Storage                             |    |             |  |   |
| Large lid                           | 9  | 2.855-231.0 | A large lid serves as a hygienic cover for the integrated disposal module.   | ■ |
| Drawer set 16 L                     | 10 | 2.855-234.0 | The 16-l drawer kit contains both a 16-l capacity drawer made of recycled material and two open drawer holders for attaching it.       | ■ |
| FlexoTray                           | 11 | 2.855-238.0 | Practical FlexoTray storage box for 12-l and 6-l buckets or the compatible EB 30/1 Li-Ion machine.                                     | ■ |
| Multifunctional bucket 12 L         | 12 | 2.855-239.0 | 12-l bucket for preconditioning mops or alternatively for use as a flexible carrying basket for various cleaning utensils.             | ■ |
| Drawer bracket open                 | 13 | 2.855-245.0 | Open drawer holder for practical attachment of a tray or 8-l, 16-l and 31-l drawers, for all closed ExpertPro variants.                | ■ |
| Lid for bucket 12 L                 | 14 | 2.855-264.0 | A practical lid that covers the 12-l buckets for more hygiene.   | ■ |

■ Included in the scope of supply. □ Available accessories.

## ACCESSORIES FOR FM EXPERTPRO 50/ P

### 1.321-008.0



|                                      |    | Order no.   | Description   |   |
|--------------------------------------|----|-------------|---|---|
| <b>TROLLEYS &amp; BUCKET SYSTEMS</b> |    |             |   |   |
| <b>Storage</b>                       |    |             |   |   |
| Tablet set                           | 15 | 2.855-291.0 | The tray kit includes both the tray and two open drawer holders for attachment.   | ■ |
| Small lid                            | 16 | 2.855-232.0 | A small lid provides reliable protection for the matching bin liner holder.   | □ |
| Drawer set 8 L                       | 17 | 2.855-233.0 | The 8-l drawer kit contains both an 8-l capacity drawer made of recycled material and two open drawer holders for attaching it.   | □ |
| Drawer set 31 L                      | 18 | 2.855-235.0 | The 31-l drawer kit contains both a 31-l capacity drawer made of recycled material and two open drawer holders for attaching it.  | □ |
| FlexoBox                             | 19 | 2.855-237.0 | The tilting FlexoBox allows textiles to be picked up ergonomically and can be opened and closed conveniently by foot.   | □ |
| Drawer bracket closed                | 20 | 2.855-246.0 | Closed drawer holder for practical attachment of a tray or 8-l, 16-l and 31-l drawers, for all open Expert versions.  | □ |
| Holder for multifunctional bucket    | 21 | 2.855-253.0 | 6-l or 12-l buckets can be attached to the outside of the FlexoMate cleaning trolleys at different heights as required using the special holders for multifunctional buckets. | □ |
| Key for lid                          | 22 | 2.855-257.0 | The lid of the FlexoMate cleaning trolley can be locked using a practically designed key. This way, the trolley contents can be protected from unwanted access.               | □ |
| Lid for bucket 6 L                   | 23 | 2.855-265.0 | A practical lid serves to hygienically cover the 6-l buckets.   | □ |
| Document holder, door                | 24 | 2.855-270.0 | Easy-to-attach document holder for convenient storage of materials such as safety data sheets, wall charts and cleaning schedules.  | □ |
| Washer for Push to open (10x)        | 25 | 6.400-019.0 | Spare part for replacing a broken washer.   | □ |
| Basket with bottle insert            | 26 | 6.999-290.0 | Carrying basket with bottle insert, carrying handle and removable dividers.   | □ |
| Set clip painted (8x-2)              | 27 | 9.212-802.0 |   | □ |
| <b>Fixation</b>                      |    |             |   |   |
| Set profile corner                   | 28 | 2.855-247.0 | Aluminum corner frame profile for individual customization of Flexomate cleaning trolleys with large and small base plates.   | ■ |

■ Included in the scope of supply. □ Available accessories.


## ACCESSORIES FOR FM EXPERTPRO 50/ P 1.321-008.0



|   |    | Order no.   | Description   |   |
|---|----|-------------|---|---|
| <b>TROLLEYS &amp; BUCKET SYSTEMS</b>    |    |             |   |   |
| <b>Fixation</b>                         |    |             |   |   |
| FlexoLink S                             | 29 | 2.855-255.0 | Small FlexoLink S bracket for mop holders and feather dusters with a maximum diameter of 26 mm.   | ■ |
| FlexoLink XL                            | 30 | 2.855-261.0 | The large FlexoLink XL can be used to attach cleaning signs or the WVP 10 Adv to the trolley.   | ■ |
| Cover strip                             | 31 | 2.855-266.0 | Cover strip to conceal open areas in the top frame and on the base plate.   | ■ |
| Side panel for ExpertPro                | 32 | 2.855-290.0 | Side panel as a cover for the front and side areas and as alternative to the door.  | ■ |
| FM door large                           | 33 | 9.212-804.0 | Long large door makes closing up the cleaning trolley ultra-simple.   | ■ |
| Rail for FlexoLink                      | 34 | 2.855-226.0 | The bar is used to attach the different FlexoLinks to the cleaning trolley.   | □ |
| FlexoDock                               | 35 | 2.855-241.0 | With the FlexoDock, two or more FlexoMate trolleys can be connected to each other and then disconnected.  | □ |
| FlexoLink M                             | 36 | 2.855-254.0 | The FlexoLink M bracket can be used to secure machines to the trolley during transport.   | □ |
| Holder for mop press                    | 37 | 2.855-260.0 | Holder for 2 × 15-l buckets and universal mop press.  | □ |
| Folding base frame for extension module | 38 | 2.855-273.0 | Folding base plate for extending the Expert and ExpertPro versions. Suitable for double bucket system and machines such as the T 9/1 Bp or the BR 30/1 C Bp.  | □ |
| Add-on module base frame                | 39 | 2.855-279.0 | The expanding base plate without wheel is suitable for supporting bin liners or as a carrying option for 2 × 6-l buckets or 1 × 12-l bucket, as well as small cleaning machines such as the EB 30/1 Li-Ion or the BR 30/1 C Bp. | □ |
| Damper, small lid                       | 40 | 2.855-318.0 | The dampers ensure that the large and small lids close softly.  | □ |
| Tool holder BR30/1                      | 41 | 2.855-319.0 | Tool holder BR30/1 for attaching the compact scrubber dryer BR 30/1 C Bp to the FlexoMate trolley.  | □ |
| Tablet holder for FlexoMate             | 42 | 9.212-038.0 | Tablet holder with removable key, provided with screws and Rilsan painted fixing bar.   | □ |

■ Included in the scope of supply. □ Available accessories.

ACCESSORIES FOR FM EXPERTPRO 50/ P  
1.321-008.0



|                                |    | Order no.   | Description  |                                     |
|--------------------------------|----|-------------|--|-------------------------------------|
| TROLLEYS & BUCKET SYSTEMS      |    |             |  |                                     |
| Fixation                       |    |             |  |                                     |
| FM key door                    | 43 | 9.212-803.0 | The doors of the FlexoMate cleaning trolley can be locked using a practically designed key. This protects the trolley contents from unwanted access. | <input type="checkbox"/>            |
| FM door small                  | 44 | 9.212-805.0 | A small door is ideal for the FlexoMate trolleys in combination with the compatible FlexoBox.  | <input type="checkbox"/>            |
| Wheels                         |    |             |  |                                     |
| Castor without brake Std. D125 | 45 | 2.855-298.0 | Castors in a pack of two without a brake. Very robust and smooth-gliding on hard floors and textile coverings.                                       | <input checked="" type="checkbox"/> |
| Castors with brake Std. D125   | 46 | 2.855-299.0 | Castors in a pack of two with a brake. Very robust and smooth-gliding on hard floors and textile coverings.  | <input checked="" type="checkbox"/> |
| Impact protection              | 47 | 2.855-300.0 | Impact protection to prevent direct contact and damage both to furniture and to the trolley itself.  | <input type="checkbox"/>            |
| Push handles                   |    |             |  |                                     |
| FlexoGrip                      | 48 | 2.855-244.0 | Three-step adjustable, ergonomic FlexoGrip reduces the strain on the user's wrists.  | <input checked="" type="checkbox"/> |
| Sliding handle Classic         | 49 | 2.855-243.0 | Easy-to-attach sliding handle with additional option of FlexoLink integration.   | <input type="checkbox"/>            |
| Cleaning                       |    |             |  |                                     |
| Bucket 6 L                     | 50 | 9.212-800.0 | A small bucket with a capacity of 6 l is ideal for surface cleaning.   | <input type="checkbox"/>            |

■ Included in the scope of supply.    ☐ Available accessories.